



4

3


2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
FB	00		P	REVISED PER ECO-11-005033	29MAR11	RK HMR



RECOMMENDABLE P.C.B MOUNTING DIMENSIONS
(CONNECTOR MOUNT SIDE)
(PCB THK=1.6)



NOTE

1. MATERIAL : HOUSING / 66NYLON UL94V-0 NATURAL
Ø0.6 POST / TIN BRASS 3/4H

35.9	28.0	14	30	3-292252-0
33.9	26.0	13	28	2- -8
31.9	24.0	12	26	2- -6
29.9	22.0	11	24	2- -4
27.9	20.0	10	22	2- -2
25.9	18.0	9	20	2- -0
23.9	16.0	8	18	1- -8
21.9	14.0	7	16	1-292252-6
A	B	N	POS	P/N

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10 ≥ *	: ±0.2
30 ≥ * > 10	: ±0.25
100 ≥ * > 30	: ±0.3
ANGLE	: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

SEE NOTE

DWN S.XU 31JAN03

CHK S.YAO 31JAN03

APVD T. SASAKI 31JAN03

PRODUCT SPEC

108-60020

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
CT DOUBLE ROW CONNECTOR
POST HEADER (VERTICAL)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-292252

SCALE NTS

SHEET 1 OF 1

REV P