

Grass Trimmer LXT®

DUR190U

18V • 3 500 – 6 000 min⁻¹ • 230 / 255 / 300 mm

Brushless trimmer with a offset bikehandle and auto-speed control for trimming greenspaces

Powerful line trimmer with a offset bike handle for trimming gardens and other green spaces. Equipped with an automatic speed control for adjusting speed in line with load. Low vibration and noise levels and good ergonomics ensure a good user experience.



LXT BL MOTOR ADT AFT

Technical specifications

Nominal Battery Voltage	18 V
No load speed	3500 / 5100 / 6000 min ⁻¹
Cutting width	230 / 255 / 300 mm
Tool weight with battery	2,9 - 3,3 kg
Nylon line- Diameter	2,0 mm
Sound Power Level (L _{WA})	85,9 - 91,6 dB(A)
Sound Pressure Level (L _{pA})	74 - 77 dB(A)
Product Dimensions (L x W x H):	1836 x 610 x 473 mm
Brushless Motor	✓
Voltage LXT	✓
Spindle Thread	M10 x 1,25 LH
Handle Type	U
Vibration Level, Metal 4-Blade	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Metal 4-Blade	1,5 m/s ²

User benefits

- Low power consumption thanks to brushless motor
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- A protective hood for metal sheet, plastic knife and line head
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

125520-4

Shoulder Strap



198893-8

Trimmer Head 2,0 mm, M10 x 1.25



783202-0

Hex Wrench 4Mm



831304-7

Accessory Bag



Other

User manual

Parts drawing