



ENGLISH

Datasheet

Stock No: 815-723

RS Pro Standard DIN Rail Terminal, TRK Series



Approvals

UL, CSA

RS DIN Rail Terminals 2

Approvals

UL, CSA

Product Details

Disconnect

Lever action for isolation of circuits Fingernail or screw driver to open

Enclosed design, no end cover needed

Cable sizes from 0.2 – 2.5mm²

Rated at 400V, 10A

Same shape as 2.5 to 10mm² standard terminals

Warning

The disconnect terminal (stock no. 815-723) is for isolation purposes only. Do not use to switch equipment on or off when power is applied.



ENGLISH

Specifications:

| | |
|-------------------------------|------------------------|
| Series | TRK |
| Wire Size | 22 → 12 AWG |
| Cable CSA | 0.5 → 5mm ² |
| Colour | Brown |
| Current Rating | 15A |
| Termination Method | Screw Down |
| Voltage Rating | 600 V |
| Minimum Operating Temperature | -40°C |
| Maximum Operating Temperature | +105°C |