

Bourdon Tube Pressure Gauges, Stainless Steel

Modelcode type: 23X.50

Item number: 63567202

Description

Design	EN 837-1
Nominal size	160 mm
Accuracy class	class 1.0
Scale range	0...40 MPa
Unit of outer Scale	MPa
Process connection	G 1/2 B
Connector location	lower back mount

Materials

Measuring system	stainless steel
Movement	
Dial	Aluminum, white
Pointer	aluminium, black
Case material	Stainless steel 1.4301
Window	laminated safety glass
Bezel ring	cam ring (bayonet type), stainless steel
Case filling fluid	glycerine

Operating conditions

Permissible medium temperature	+ 100 °C
Permissible ambient temperature	-20 ... +60 °C
Ingress protection	IP 65

Options

Mounting flange/bracket	front flange, stainless steel
-------------------------	-------------------------------

Labelcode

Label	WIKA standard without / with Tag-number
language of the label	German

