

Logitech® for Business

B910 HD Webcam

- HD 720p30 video calling, dual stereo microphones
- True 16:9 widescreen with a 78-degree field of view
- Carl Zeiss® optics with autofocus
- Plug-and-play, UVC-compliant video conferencing
- Certified for Microsoft® Office Communicator and tested and qualified with most major business video-calling clients



B910 HD Webcam. The sharpest way for professionals to meet face-to-face without leaving the desk. Video calls look and sound lifelike and professional with HD 720p30 video calling and dual stereo microphones. True 16:9 widescreen with a 78-degree field of view makes it perfect for small group video-conferencing. Carl Zeiss® optics with autofocus keeps images incredibly sharp and clear – and automatically focuses, even in extreme close-up (up to 10 cm/3.94 inches). It's easy to deploy and manage, too, offering UVC-compliant, plug-and-play video conferencing and broad compatibility with business video-calling clients. Plus, it's certified for Microsoft® Office

Communicator. So if you're keeping a close eye on travel costs, or your travel plans just fall through, the B910 HD Webcam is a smart choice.

OPTIMIZED FOR
Microsoft®
Office Communicator

SYSTEM REQUIREMENTS

UVC mode (No software installation required):

- Windows® XP, Windows Vista®, or Windows® 7

Drivers provided for 32-bit and 64-bit versions of Windows XP, Windows Vista, or Windows 7

Microsoft® Office Communicator 2007 R2 or (higher) video conferencing requirements:

- OS: Windows XP (SP2 or higher), Windows Vista or Windows 7 (32-bit or 64-bit versions)

HD video (720 x 1280) at 30 fps

- CPU: Quad core 2.0 GHz or higher
- RAM: 2 GB or more
- Upstream bandwidth: 1.5 mbps

VGA video (640 x 480) at 30 fps

- CPU: Dual core 1.9 GHz or higher
- RAM: 1 GB or higher
- Upstream bandwidth: 600 kbps

For CIF (352 x 288) at 15 fps

- CPU: Single core 1.5 GHz or higher
- RAM: 512 MB or higher
- Upstream bandwidth: 250 kbps

For other video-conferencing software, please refer to the documentation from the vendor for specific system requirements.



Logitech® for Business

B910 HD Webcam



TECHNICAL SPECIFICATIONS

- Carl Zeiss® glass lens
- Autofocus system
- Native 5-MP HD sensor
- 78-degree wide-angle field of view
- High-definition video in 720p widescreen mode with recommended system
- Full HD 1080p video capture with recommended system
- Colour depth: 24-bit true colour
- Frame rate: up to 30 frames per second streaming video at 720p and VGA mode
- Photo capture: 5 million pixels (10 megapixels software enhanced)
- USB cable (1.5 metres/5 feet)
- Built-in dual microphones with RightSound™ Technology**
- Hi-Speed USB 2.0 certified
- Universal clip fits laptops, LCD or CRT monitors
- UVC compliant
- Works with most instant-messaging and video-conferencing applications
- Optimised for Microsoft® Office Communicator
- Logitech webcam drivers support HD audio, RightLight™ 2 and RightSound technology

** Software installation required for RightSound technology.

PACKAGE SPECIFICATIONS

	Primary Pack	Master Shipper Carton
Part #	960-000684	n/a
Bar code	5099206026087 (EAN-13)	50992060260812 (SCC-14)
Weight	359.4	13.040
Length	18.00	42.50
Width	13.50	29.00
Height/depth	8.00	60.00
Volume	1.944dm ³	0.07395m ³
1 primary pack	1	n/a
1 intermediate pack	10	n/a
1 master shipper carton	30	1
1 pallet EURO	540	18
1 container 20 ft	12060	402
1 container 40 ft	24840	828
1 container 40 ft HQ	26880	896

PACKAGE CONTENT



- Webcam
- Universal monitor clip
- Installation CD
- User documentation
- 3-year manufacturer's guarantee and full product support

www.logitech.com/business

©2010 Logitech. Logitech, the Logitech logo and other Logitech marks are owned by Logitech and may be registered. All other trademarks are the property of their respective owners.