



Main

Range of product	Mini Pragma
Product or component type	Base
Accessory / separate part category	Enclosure accessory
[In] rated current	63 A
Number of horizontal rows	3
Number of 18 mm modules per row	12
Terminal block function	Without

Complementary

Enclosure mounting	Flush
Total number of 18 mm modules	36
Cable entry	Pre-cutted holes
Enclosure material	Back part: technoplastic
Width	270 Mm wall:
Height	478 Mm wall:
Depth	80 Mm wall: 18 Mm outside: 98 Mm total:

Environment

Standards	IEC 60695-2-11 EN 50102
Fire resistance	Back part: 650 °C
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	583 G
Package 1 Height	8.6 Cm
Package 1 width	28.9 Cm
Package 1 Length	48.8 Cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Weight	3.85 Kg
Package 2 Height	31.2 Cm
Package 2 width	41.3 Cm
Package 2 Length	53.7 Cm
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Weight	66.82 Kg
Package 3 Height	120 Cm
Package 3 width	80 Cm
Package 3 Length	120 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**