



---

**PRODUCT-DETAILS**

# ASF34/M32/A/BL

## 90D PA66 FITTING M32 34MM-BL



---

**General Information**

Extended Product Type	ASF34/M32/A/BL
Product ID	7TCA296000R1714
EAN	5020963010644
Catalog Description	90D PA66 FITTING M32 34MM-BL
Long Description	Adaptaseal Straight Conduit Fitting, Fixed External Male Thread, Fine Profile, Nominal Conduit Size 34mm, M32 Thread, Polyamide (Nylon) 66, Black

---

**Additional Information**

Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

---

**Ordering**

EAN	5020963010644
UPC	786210281643

---

## Technical

Number of Batteries	0
Color	Black
Material	Polyamide/Nylon 6.6
Size	NC 34mm

---

## Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

## Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963010644

---

## Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

---

## External Classifications and Standards

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

---

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

