

Model No. 1145EURD

40mm wide solid brass body padlock with hexagonal shackle

Best Used For:


Self-Storage Units & Lockers


Sheds, Workshops & Garages


Trailers, Vans & Moving Trucks

Security Level:



Medium to high security:

Recommended for outdoor general purpose (except for electronic padlocks 1500eURDBLK and 4400EUREC)

Overview & Features

Product Features


- 40mm wide solid brass body padlock
- Hardened steel shackle for extra cut resistance
- Patented hexagonal shackle shape increases the cross section
- Dual locking levers for added protection from prying and hammering
- 6-pin high security cylinder for maximum pick resistance
- 4 dimple keys for added security and convenience
- Limited Lifetime Warranty

Product Details

The Master Lock No. 1145EURD Solid Brass Padlock features a 40mm wide solid brass body for maximum strength, reliability and weather resistance. The 7,5mm diameter hexagonal shackle is 23mm long and made of hardened steel, offering maximum resistance to cutting and sawing. The 6-pin cylinder offers maximum resistance against picking and the dual locking ball bearings provide maximum resistance against prying and hammering. The padlock comes with 4 dimple keys for added security and convenience. The Limited Lifetime Warranty provides peace of mind from a brand you can trust.

Product Specifications

Product Number	1145EURD
Body Width	40mm
Shackle Dimensions	A: 7.5 mm B: 23 mm C: 22 mm
Colour	Gold
Description	Keyed Different
Shelf Pack Qty	4
Master Carton Qty	24



Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu