



355.006.5

HIPROJACKET HJ-L-04 - 06 MM. - RED - 100 MTR. .

Product Properties:

Heat-resistant	Yes
Stretch sleeve	No
Max temperature under flame	538°C approx. 20 minutes
Max temperature radiation heat	538°C i approx. 20 minutes
Max temperature molten metal splash	1200°C approx. 15-30 seconds
Colour	Red
Operating temperature	-55-260 °C

Dimensions:

MOQ	100 .
Unit	m
Inner diameter	6 mm

Approvals:

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
General compliance statement from manufacturer	https://www.nelco.se/Image/GetDocument/1041
Iron and Steel Sanction	Compliance
PFAS	Compliant
REACH	No SVHC (240 Subs. 23 Jan 2024)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS

ECCN (US)

EAR99

Other information:

ETIM-Class	EC002254 - Cable insulation hose
ETIM-Release	9.0
Trademark	Anamet
Product Group	206040
Search Description	HIPROJACKET HJ-L-04,ID=6MM, YD=8MM
Alternative SKU	355.006.5

Logistic information:

Barcode	871711440358
Country of origin	FR
Item status	Non Stock Item, can be on stock but is not a regular stock item.
MOQ	100 .
Stock code	355.006.5
Taric code	85461000
Unit	m

*We reserve the right to make technical changes and disclaim any typographical errors.