



-1. Screwdrivers

-1.1. ERGO™ SCREWDRIVERS

- Screwdriver developed according to the scientific ERGO™ process
- Insulated screwdriver for slotted head screws
- For work on live equipment, up to 1000V
- Handle: 3-component handle, for maximum user comfort and force transmission
- Easy to choose the right tip, with the colour-coded handle and the symbol on the domed end
- High performance alloy steel, insulation moulded directly onto blade. Black finish tip for higher accuracy
- ISO 2380 / DIN 5264
- Individually inspected and manufactured according to IEC 60900

Insulated screwdrivers

BE-8010S - BE-8065S



BE-8010S	7314150033058	5	0.4	2.5	75	20x122	197	30
BE-8220S	7314150048243	5	0.5	3.0	100	20x122	222	33
BE-8230S	7314150048250	5	0.6	3.5	100	20x122	222	33
BE-8040S	7314150033089	5	0.8	4.0	100	20x122	222	33
BE-8050S	7314150033096	5	1.0	5.5	125	27x122	247	62
BE-8255S	7314150048281	5	1.2	6.5	150	36x122	272	105
BE-8065S	7314150033119	5	1.2	8.0	175	36x122	297	127
BE-8258S	7314150242818	5	1.6	10	200	36x165	365	270
BE-8259S	7314150242832	5	2.0	12	200	36x165	365	280

