



PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 2:26 (UTC)



6800DD

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	10	mm	Bore diameter
D	19	mm	Outside diameter
B	5	mm	Width
r (min.)	0.3	mm	Chamfer dimension

Basic Load Ratings

Cr	1890	N	Basic dynamic load rating
C0r	840	N	Basic static load rating

Speeds

Grease	24000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	12	mm	Diameter of shaft abutment
da (max.)	12	mm	Diameter of shaft abutment
Da (max.)	17	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

Calculation factors

fo	14.8		Factor
----	------	--	--------

Additional information

z	10		Number of Balls
Dw	2.381	mm	Ball Diameter

Mass

Mass approx.	0.005	kg	Mass approx.
--------------	-------	----	--------------

