

## 3NA3140 LV HRC FUSE LINK 500V S.1 200A



LV HRC FUSE LINK GL/GG WITH NON-INSULATED GRIP LUGS WITH FRONT INDICATOR SIZE 1, 200A, AC 500V/DC 440V

Similar to image

Technical data:		
Current / for AC / rated value	A	200
Operating class of the fuse link		gG
Size of the fallback-system / acc. to DIN EN 60269-1		NH1
Supply voltage		
• for AC / rated value	V	500
• for DC	V	440
Switching capacity current		
• in accordance with IEC 60947-2 / rated value	kA	120
• with DC / in accordance with IEC 60947-2 / rated value	kA	25
Design of an identification indicator		Front indicators
Ambient temperature		
• minimum	°C	-5
• maximum	°C	40

### Certificates/approvals:

General Product Approval		Declaration of Conformity	Test Certificates	Shipping Approval
<input checked="" type="checkbox"/> KEMA	ROSTEST	<input checked="" type="checkbox"/> VDE	Manufacturer	Manufacturer
				<input checked="" type="checkbox"/> GL (Germanischer Lloyd)


#### other

Manufacturer

### Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>



**last change:**

Aug 26, 2011