

175 1**Pipe wrench**

Swedish pattern

Code **6437340** ETIM **EC000842**

EAN **4010886643730** UNSPSC **27-11-21-13**

Country of origin **Austria** eCl@ss **21-04-03-01**

Customs tariff number
82032000

**Article description**

- Acc. to DIN 5234 Form A
- Particularly solid design for high loads
- Head angled 85 °
- GEDORE special chrome-vanadium steel
- Drop-forged
- Fully tempered, teeth additionally inductively hardened
- Self-gripping by teeth offset against direction of rotation
- Roll nut cannot be lost

Article information

Contents [Qty of pieces]	1	Standard	DIN 5234 - Form A
Net weight [kg]	0,695 kg	Design non-sparking	No
Total length [mm]	280 mm	Pipe-Ø [mm]	44 mm
Total width [mm]	61 mm	Pipe-Ø [inch]	1
Total height [mm]	22 mm	Clamping width [mm]	44 mm
Surface	Stove enamelled blue	Hardening process	Induction hardened
Material	Chrome-vanadium steel		