



Main

Range	Acti 9
Product name	Acti 9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	2P

Complementary

[In] rated current	10 A 16 A 20 A 25 A 32 A 12 A 40 A 50 A
Fuse curve	AM GG
Fuse size	14 x 51 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	6
Connections - terminals	Screw clamp terminals 1 cable(s) 2.5...25 mm ² rigid Screw clamp terminals 1 cable(s) 2.5...25 mm ² flexible
Tightening torque	3.5 N.M

Environment

Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	242 G
Package 1 Height	5.3 Cm
Package 1 width	7.7 Cm
Package 1 Length	11.1 Cm
Unit Type of Package 2	BB1

Number of Units in Package 2	3
Package 2 Weight	800 G
Package 2 Height	11 Cm
Package 2 width	8 Cm
Package 2 Length	16 Cm
Unit Type of Package 3	S03
Number of Units in Package 3	36
Package 3 Weight	9.939 Kg
Package 3 Height	30 Cm
Package 3 width	30 Cm
Package 3 Length	40 Cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**