



Datasheet

RS PRO 3mtr 8K DP1.4 (HBR3) DisplayPort Male to DisplayPort Male Cable - Black

Stock number: 195-4910

EN


The RSPRO 3 metre 8K male to male DisplayPort cable has a black PVC jack and an outer diameter of 7.3mm. The connectors have a gold flash covering to prevent corrosion.


Our cables are DisplayPort version 1.4 (HBR3) and can support up to 8K@60Hz, 4K@120Hz or with Multi Stream Transport (MST) they can display to multiple screens.

The connector hoods are also made of black PVC and have a strain relief to prevent the jacket splitting around the boot.

DisplayPort, commonly known as DP is a digital high definition video connection which also can carries audio. Due to its bandwidth, DisplayPort cables are normally up to 5 metres long.

DisplayPort cables are very simple to use and are plug and play. Care must be taken when unplugging them to make sure that the latches have been released before pulling out the connector.





W=25MM Copper foil
DisplayPort M Dust cap
PVC~45P~Black
LDPE
Copper foil~25u~W=8MM
DisplayPort 1.4 M Black clamp ~ material PA66
DisplayPort1.4 M Upper shell (without "DP" logo) ~ fine grain surface ~ PC + ABS material ~ Black
DisplayPort1.4 M Lower shell (without "DP" logo) ~ fine grain surface ~ PC + ABS material ~ Black
DisplayPort 1.4 M Tinplate on tail clip ~ material: SPCC ~ nickel plating
DisplayPort 1.4 M Lower Horse Iron with tail clamp ~ material: SPCC ~ nickel plating
DisplayPort 1.4 M Solder~Insulation:Black~shell gold plated pin gold plated
DP1.4~(28AWG(7/0.127TC)+EAM]*5P+28AWG(7/0.127TC)*4C+AEB(85% AL)OD:7.3MM~Black Printing:DisplayPort Cable E342987 □ AWM STYLE 20276 80 □ 30V VW-1

RoHS / REACH / CE