



Main

| | |
|---------------------------|-----------------------------|
| Range | Merten |
| Product or component type | Dimmer |
| Device presentation | Mechanism with fixing frame |

Complementary

| | |
|---------------------------------------|----------------------------|
| Device application | Light control |
| Device mounting | Flush |
| Fixing mode | By screws and claws |
| Switch function | 1-pole 2-way |
| Dimmer control | Rotary push type |
| Load type | Capacitive: 20...300 W |
| [Ue] rated operational voltage | 230 V AC 50/60 Hz |
| Ambient air temperature for operation | -5...45 °C |
| IP degree of protection | IP20 |
| Height | 71 mm |
| Width | 71 mm |
| Embedding depth | 29 mm |
| Standards | EN 60669-2-1 EN 60669-1 |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |