

Upright Vacuum Cleaner XGT®

VC010G

40Vmax, 150 mbar, HEPA filter, 5 L

Model VC010G is a cordless upright cleaner powered by 40Vmax XGT Li-Ion battery.

Main feature and benefits: High dust pick-up rate corresponding to the gold level of the CRI seal of approval. Increased cleaning width of 381mm. 5-stage brushroll height adjustment. Low cleaner head with a height of approx 80mm. Wide bumper covering the front of the head. Side brush on each side of the cleaner head. 3-suction power modes with a mode memory function. Removable aluminum pipe with integrated handle for cleaning in corners or confined spaces. Tool-less brushroll change. HEPA filter.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Working width	381 mm
Air volume	1,8 m³/min
Max. sealed suction	150 mbar
Suction power	25 / 50 / 110 W
Continuous use XGT® 40Vmax / 5.0 Ah	100 / 50 / 25 min
Continuous Use XGT® 40V Max / 8.0 Ah	160 / 80 / 40 min
Dust Bag Capacity	5,0 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Product net weight	7,3 kg
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	8,0- 9,2 kg
Product Dimensions (L x W x H):	326 x 381 x 1146

User benefits

- HEPA Filter is used to capture very fine particles effectively
- 3 modes for suction power with mode memory function
- Brushless maintenance-free and long-life motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Low noise mode for use in noise sensitive environments such as offices, hospitals etc.

Link to product - www.makitaauk.com



Related products

Other

User manual

Parts drawing