



Part Number : [1300170030](#)

Product Description : Mini-Change Field Attachable, Male Connector, 5 Pole, Cable Range: 5.08-11.43mm Outside Diameter with External Threads, Stainless Steel

Series Number : 130017

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 1A5006-348



Documents & Resources

Drawings

[1300170030_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130017
Description	Mini-Change Field Attachable, Male Connector, 5 Pole, Cable Range: 5.08-11.43mm Outside Diameter with External Threads, Stainless Steel
Approvals	cCSAus certified
IP Rating	IP67
Product Name	Mini-Change
Type	Field Attachable Connector
UPC	78678853661

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

Physical

Cable Diameter	5.08-11.43mm (.200-.450")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	Nylon
Material - Contact	Copper Alloy
Material - Coupling Nut	Stainless Steel Type 316

Material - Plating Mating	Gold
Net Weight	158.757/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size (AWG)	15 to 24