



Sounds like productivity



Includes USB-C
Y charging cable

RX380

PMR446 Two-Way Radios



Compact & weather resistant

IPX2 water resistance with up to 8 km range and LCD display



9-Hour runtime

Up to 9 hours of battery life, reliable for short outings or part-time business use



16 Channels

Securely communicate across 16 channels with 121 privacy codes



Built-in flashlight

Illuminate dark areas or signal for help with a single button



Voice-activated transmission (VOX)

Hands-free usage to automatically transmit when you speak

EMERGENCY ALERT

Dedicated button for time-sensitive or emergency situations

ERGONOMIC CONTROLS

Tactile dedicated volume knob for one-handed operation

2.5 MM HEADSET JACK

Choose from a range of accessories, including speaker mic and headset functionality

USB-C JACK

For charging without dock



RECHARGEABLE AA BATTERIES

Up to 9 hours of battery life, reliable for short outings or part-time business use



USB-C Y CHARGING CABLE

Charge up to two 2 handheld radios simultaneously



BELT CLIP

Keep your radio secure and within reach with this simple, durable belt clip

Part#	Two-Way Radio Description	QTY	Part#	Accessory Headsets Description	QTY
0190002-1	PMR446 two-way radio, includes USB-C Y charging cable	2 pk	GA-SV01	Surveillance style headset with microphone	1
			GA-SV01 2P	Surveillance style headset with microphone	2 pk
			0010120-1	D-Style headset	1
			0010121-1	C-Style around the ear headset	1
			0010122-1	C-Style in ear headset	1
			0010123-1	C-Style in ear headset with foam earpiece	1