



384-6T

6 TPI Fileable Toothed Pole Pruning Saw with Steel Tube Handle 360 mm



PRODUCT DETAILS

- For easy reach of higher branches when fitted to Ø25 mm (1") extension pole
- Strong curved blade with 6 TPI or 5 TPI for more aggressive cut
- 383 hardpoint teeth, 384 fileable teeth
- With steel tube adaptor/handle
- For softer wood like pine and spruce the more aggressive 384-5T (5 TPI) is recommended
- To be used with a Ø25 mm (1") extension pole
- Fits all poles: AP-2.7M, AP-3M, AP-5 and FP-3M



PRODUCT ATTRIBUTES

Product					
384-6T	360 mm	14 in	6	320 g	11.3 oz

Follow the Fish!

