



Main

Range	Mureva
Product or component type	Socket
Device short name	Mureva socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
Plug, socket, control station shape	Angled
[In] rated current	32 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Sleeves: brass
Connections - terminals	Captive screws
Cable cross section	2.5...10 mm ²
Cable outer diameter	21 mm
Thread type	M25
Net weight	0.3 kg
Height	160 mm
Width	90 mm
Depth	119 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-1
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations