

FEATURES

- **Nylon Material:** Provides durability and resistance to wear and tear
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **Non-Releasable Design:** Ensures a secure and permanent hold
- **Length of 203mm:** Accommodates a wide range of cable sizes
- **Maximum Bundle Diameter of 52mm:** Allows for bundling of larger cable groups
- **Tensile Strength of 22kg:** Ensures robust and reliable fastening
- **Operating Temperature Range of -40°C to 85°C:** Suitable for various environmental conditions
- **Compliance with RoHS and UL 94HB:** Meets key safety and environmental standards

RS PRO Nylon Cable Tie, 203mm Non-Releasable

RS Stock No: 656-094



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO nylon cable ties are designed for securely bundling and organising cables and wires. Ideal for both industrial and domestic applications, they offer a reliable solution for managing cable installations efficiently.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releaseable
Tensile Strength	22 kg

Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

Mechanical Specifications

Length	203 mm
Material	Nylon
Maximum Bundle Diameter	52 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------

