

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674



Range Features

- Wide beam angle of 220 degrees!
- Instant start
- Long lifetime 15,000 hours
- Short payback period
- Up to 85% energy savings compared to incandescent equivalent

LED

PRODUCT OVERVIEW

Lamp finish	Frosted
Lamp shape	A60
Colour temperature (K)	2700
Colour	Homelight
CRI (Ra)	80
Dimmable	No
EAN code	5410288266749
Energy class	A+
Equivalent watt (W)	40
Cap/Base	B22
Type	ToLEDo GLS
Watt (Nominal) (W)	6.5
Light colour	Homelight
Ordering number	0026674
Efficacy (Rated) (lm/w)	72.3
Average life (Rated) (h)	15000
Luminous flux (Rated) (lm)	470
Technology	LED
Voltage (V)	220-240

DATA TABLE

General data

Average life (Nominal) (h)	15000
----------------------------	-------

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674

Control gear required	No
Lamp finish	Frosted
Lamp shape	A60
Control gear availability	No
Dimmable	No
Dry applications use only	Yes
EAN code	5410288266749
Energy class	A+
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	B22
Lamp mercury content (mg)	0
Type	ToLEDo GLS
No. of switching cycles before premature failure (min)	20000
Optimal operating condition (°C)	25
Ordering number	0026674
Range features	Wide beam angle of 220 degrees! Instant start Long lifetime 15,000 hours Short payback period Up to 85% energy savings compared to incandescent equivalent
Product name	ToLEDo GLS V2 6.5W 470LM 827 B22 SL
Average life (Rated) (h)	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%

Optical data

Colour temperature (K)	2700
CRI (Ra)	80
Light colour	Homelight
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	470
Luminous flux (Rated) (lm)	470
Suitable for accent lighting	No
Adjustable chromaticity	No

Physical data

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674

Colour	Homelight
Diameter (mm)	60
Max. Lamp Diameter (mm) - D	60
Lamp Length (mm) - C/L	108
Lamp dimension equal to filament lamp equivalent	Yes

Electrical data

Current (A)	36
Equivalent watt (W)	40
kWh per 1000 hours burning time	7
Lamp power factor	0.8
Watt (Nominal) (W)	6.5
Efficacy (Rated) (lm/w)	72.3
Watt (Rated) (W)	6.5
Voltage (V)	220-240

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674

