



Part Number : [734036803](#)

Product Description : FAKRA Jack, Right-Angle, PCB Receptacle, Through Hole, Die Cast Body, Tin (Sn) Plated, Keying Code D, Bordeaux Violet, 50 Ohms

Series Number : 73403

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734036803 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 3; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73403
Description	FAKRA Jack, Right-Angle, PCB Receptacle, Through Hole, Die Cast Body, Tin (Sn) Plated, Keying Code D, Bordeaux Violet, 50 Ohms
Application	Automotive
Product Name	FAKRA,SMB
Style	PCB
Type	Subminiature
UPC	889056185103

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	Yes
Net Weight	5.019/g
Orientation	Right Angle
Packaging Type	Tray

Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

This document was generated on Aug 11, 2025