

## UIC 558 22PIN PLUG KIT-MC-NI-CGM



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 022 1001
Specification	UIC 558 22PIN PLUG KIT-MC-NI-CGM
HARTING eCatalogue	<a href="https://harting.com/09580221001">https://harting.com/09580221001</a>

### Identification

Category	Connector sets
Series	HARTING UIC
Identification	UIC 558
Element	Connector sets
Specification	With cable gland

### Version

Termination method	Crimp termination
Gender	Male
Number of contacts	22
PE contact	Yes
Number of cable entries	1
Cable entry	1x Integrated
Details	Crimp contacts enclosed separately

### Technical characteristics

Conductor cross-section	0.75 ... 1 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	110 V
Insulation resistance	>10 <sup>7</sup> Ω
Contact resistance	≤4 mΩ
Stripping length	5 mm



Pushing Performance  
Since 1945

## Technical characteristics

Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition
Clamping range	17.7 ... 18.5 mm

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Nickel plated
Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	Black RAL 5010 (gentian blue)
Material (seal)	Silicone
Material flammability class acc. to UL 94	V-0

## Specifications and approvals

Specifications	UIC 50558 IRS 50558 IEC 61373 Category 2 IEC 60529
----------------	---

## Commercial data

Packaging size	1
Net weight	370 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140190306
eCl@ss	27440115 Circular connector (set)
ETIM	EC002635
UNSPSC 24.0	39121413