

PSEN ma1.4p-50/PSEN ma1.4-03mm/ 1unit

506332



Magnetic safety switch 2 n/o, 4-pin M8 male connector, square design, IP67, operating distance 3 mm, height design 18 mm, PU = 1 sensor with actuator.

Technical details

General data

Approval:	CE, UKCA, cULus Listed, TÜV, EAC (Eurasian)
Sensor principle:	magnetic
Coding level to ISO 14119:	Low
Classification to EN 60947-5-3:	PDDb
Suitable for series connection:	no
unit type:	Unit

Technical data

Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Switching voltage:	24 V

Environmental data

Ambient temperature:	-10 - 55 °C
Max. ambient temp. at 2000 m:	+55 °C
Climatic suitability standard:	IEC 60068-2-30
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	4000 m
EMC to standard ...:	EN 60947-5-3
Vibration to standard ...:	EN 60947-5-2

Acc. shock to standard1:	30g
Pollution degree clear.&creep.:	3
Mechanical data	
Type 1 actuator:	PSEN ma1.4-03mm
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	M8, 4-pin male
Cable lines:	LiY11Y 4 x 0.25 mm ²
Housing material upper part:	PBT
Height dimension:	37 mm
Width dimension:	26.4 mm
Depth dimension:	18 mm
Net weight:	51 g
Gross weight:	67 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes
RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85365019
UNSPSC 25:	39122205
EAN-Code:	4046548060478
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272402
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002544
Volume:	0 dm ³

Optional accessories



533111

PSEN Kabel Gerade/cable straightplug 2m



533110

PSEN Kabel Winkel/cable angleplug 2m



533121

PSEN Kabel Gerade/cable straightplug 5m



533120

PSEN Kabel Winkel/cable angleplug 5m



533131

PSEN Kabel Gerade/cable straightplug 10m



533130

PSEN Kabel Winkel/cable angleplug 10m



533141

PSEN Kabel Gerade/cable straightplug 30m



533140

PSEN Kabel Winkel/cable angleplug 30m



380200

PSS67 Cable M8sf M12sm, 3m



380203

PSS67 Cable M8sf M12sm, 30m



380204

PSS67 Cable M8af M12sm, 3m



380201

PSS67 Cable M8sf M12sm, 5m



773600

PDP67 F 8DI ION



380202

PSS67 Cable M8sf M12sm, 10m



380207

PSS67 Cable M8af M12sm, 30m



380205

PSS67 Cable M8af M12sm, 5m



380206

PSS67 Cable M8af M12sm, 10m