



Catalogue No 666M & 667M Feeler Leaf Specification

Accuracy to U.S.A. Fed. Spec GGG-G-17C

<u>METRIC</u>			
Cat. No.		666M	667M
Leaf Length		7.6/6.1m	304mm
Leaf Type		Straight	Straight
No. of Leaves		Roll	-
Nominal Size (mm)	Thickness Tolerance (mm) U.S.A. Fed. Spec GGG-G-17C		
0.03	+/- 0.005	X	X
0.04	"	X	X
0.05	"	X	X
0.06	"	X	X
0.08	"	X	X
0.10	"	X	X
0.15	"	X	X
0.20	+/-0.006	X	X
0.25	+/- 0.009	X	X
0.30	"	X	X
0.35	+/- 0.011	X	X
0.40	+/- 0.012	X	X
0.45	"	X	X
0.50	+/- 0.014	X	X