

FEATURES

- This RS PRO rackmount enclosure is made from high-grade cold-rolled steel, with the front and back panels made from lightweight aluminium
- Each unit offers top, base and side ventilation apertures for optimum cooling, especially when housing electronic equipment or components
- The two-layer front panel has been designed with an adjustable gap (0 – 20 mm)
- The whole enclosure unit is powder-coated following a 5-stage iron phosphate pre-treatment to prevent oxidation and provide longer-lasting protection, especially in harsh environments
- The precise design and high-quality manufacturing standard enables fast and easy assembly while offering complete compatibility with all 19-inch standard equipment
- In addition to this, each unit has 2 extruded aluminium handles and 4 adhesive rubber feet for additional versatility across a wide range of applications
- Gloss black finish for easy cleaning and keeping the surface dust and debris free
- The enclosure unit and accessories supplied with the unit are packed flat for convenient shipment and storage
- Supplied with 4 fitted and 4 loose Board / Chassis plate / Component fixing crossbars
- The PF19 enclosure range is available in a wide variety of sizes

RS PRO Rackmount Enclosures - Ventilated Rackmount Enclosure

RS Stock No.: 6657722



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO PF19 Series Rackmount Enclosure

Introducing the RS PRO PF19 Rackmount Enclosures, a high quality and heavy-duty electronic enclosure series, suitable for a wide range of uses. Constructed from a mixture of high grade rolled steel and lightweight aluminium panels, these rackmount enclosures offer a sturdy construction and combined with the tough powder-coated finish, provide long-lasting life of the product even in harsh environments. The enclosures are easy to use and assemble, thanks to the precision workmanship and well-engineered design. In addition to this, the high-quality materials that are used to manufacture this RS PRO enclosure offer a strong and aesthetically-pleasing finished product, suitable for a wide range of applications both at home or in industry.

General Specifications

| | |
|-------------------------|--|
| Series | PF-19 |
| Mounting | Rackmount |
| Rack Units | 4U |
| Material | Steel |
| Horizontal Pitch | 84 HP |
| Ventilated | Yes |
| Handles | Yes |
| Colour | Black |
| For Use With | Provide long-lasting life of the product even in harsh environments |
| Rack Size | Half Width |
| Features | Each unit offers top, base and side ventilation apertures for optimum cooling |
| Sound Proof | No |
| Fan Included | No |

Mechanical Specifications

| | |
|------------------|----------------------------|
| Dimension | 177 x 482.6 x 425mm |
| Height | 177mm |
| Depth | 425mm |
| Width | 482.6mm |

Approvals

| | |
|----------------------|---|
| Declarations | RoHS Certificate of Compliance |
| Standards Met | IEC 297 EIA RS-310 C1977 DIN 41494 Conforms to ASTM D610-01 (Creepage test) Conforms to ASTM B117 (500 hours salt spray test) |

Similar Products

| Stock No. | Brand | Product Name | Material | Dimension | Rack Units |
|-----------|--------|--------------------------------|----------|----------------------|------------|
| 6657700 | RS PRO | Ventilated Rackmount Enclosure | Steel | 43.7 x 482.6 x 245mm | 1U |
| 6657712 | RS PRO | Ventilated Rackmount Enclosure | Steel | 88.1 x 482.6 x 335mm | 2U |

Accessories / Dimension Drawing / Top View / Front View / Side View

There are 24 different sizes and configurations which are available in :

- Height : 1.5U to 6U (B)
- Width : 482 (A)
- Depth : 90, 245, 335, 425 and 465 (D)

