

Han PushPull Power Base panel w. gasket



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 002 0323
Specification	Han PushPull Power Base panel w. gasket
HARTING eCatalogue	https://harting.com/09350020323

Identification

Category	Connectors
Series	Han® PushPull (V14)
Type of hood/housing	Bulkhead mounted housing

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Specifications and approvals

Specifications	IEC 61076-3-117
----------------	-----------------

Commercial data

Packaging size	1
Net weight	4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140053632
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466