



Hand protection

VENICUTF08

INTENSE CUT WORK

Level F cut-resistant glove, ideal for dry conditions



Specific benefits



Easy to use

· Perfect fit so that users do not feel any discomfort in the wrist area with prolonged use



Performance

· The anti-slip properties of the polyurethane coating provides good grip.



Cost-effective

· User-friendly worksite package, including three pairs for weekly use

Certifications and norms



EN 388
3 X 4 2 F

ANSI ISEA 105
A6

Technologies & labels

· EConocut

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Light industry
- Maintenance



Hand protection

VENICUTF08

INTENSE CUT WORK

Level F cut-resistant glove, ideal for dry conditions

Standards - Details



EN388:2016+A1:2018

3 [0-4] ABRASION RESISTANCE
X [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
2 [0-4] PIERCE RESISTANCE
F [A-F] CUT RESISTANCE ISO 13997

Technical details

Glove kind	Mechanical glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Coating material and finition	PU
Coating level	Palm coated
Number of layer	Single layer
Gauge	13
Color	Grey
Size	7, 8, 9, 10, 11
Type of packaging	Pack of 3



Safety gloves

VENICUTF08

INTENSE CUT WORK

Level F cut-resistant glove, ideal for dry conditions

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VECUTF08GRG307	Grey	07	VENICUTF08	3295249296513	13295249296510	40	4	0.0 kg	31.0 cm	62.0 cm	34.0 cm
VECUTF08GRG308	Grey	08	VENICUTF08	3295249296520	13295249296527	40	4	0.0 kg	31.0 cm	62.0 cm	34.0 cm
VECUTF08GRG309	Grey	09	VENICUTF08	3295249296919	13295249296916	40	4	0.0 kg	31.0 cm	65.0 cm	35.0 cm
VECUTF08GRG310	Grey	10	VENICUTF08	3295249296537	13295249296534	40	4	0.0 kg	31.0 cm	62.0 cm	36.0 cm
VECUTF08GRG311	Grey	11	VENICUTF08	3295249296551	13295249296558	40	4	10.77 kg	25.4 cm	74.0 cm	30.5 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height