

0 603 9D4 070 – UniversalDrill 18V

Material number	0 603 9D4 070
EAN	4053423225181
1 battery pack PBA 18V 1.5Ah W-A	✓
Carrying case	✓
Charger AL 1810 CV	✓
Double screwdriver bit	✓



Technical data

Technical data

Battery voltage	18,0 V
Battery capacity	1,5 Ah
No-load speed (1st gear / 2nd gear)	0 – 440 / 1,450 rpm
Max. torque	40,0 Nm
Max. torque for soft/hard screw. applications	23 / 32 Nm
Torque settings	20 + 1
Drill chuck	10-mm keyless chuck
Machine weight with battery	1,20 kg
Product name (formatted)	UniversalDrill 18V



Screw diameter

Screw diameter up to	8 mm
----------------------	------

Drilling diameter

Drilling diameter in steel	10 mm
Drilling diameter in wood	30 mm

Functions

18 Volt	✓
Lithium-ion technology	✓
Bosch Auto-Lock	✓
2-speed gearbox	✓
Application: screwdriving / drilling	✓
Softgrip	✓
Integrated work light	✓

Noise/vibration information

Sound pressure level	70 dB(A)
Uncertainty K	3 dB

Sales information

Positioning

- Compact and powerful cordless all-rounder fulfils every wish

User benefit

- The 2-gearbox and 20 torque presettings deliver suitable power and speed for every application
- Clean, ergonomic design for comfortable handling
- LED light for optimal illumination of the work area
- Ideal for drilling projects in wood, metal and plastic, as well as for screwdriving
- Power for ALL: One battery and charger for an entire Home & Garden tools system

