

Outdoor Housing with Heating and Power Supply

Art. no. TVAC70200

Page 1 of 1



- Protection class IP68/IK10
- Integrated 12 V DC (1.5 A, gross) power supply unit
- Internal cable routing
- Two integrated heating elements
- Suitable for use in any outdoor area

The weatherproof housing offers optimal protection even in extremely adverse environmental conditions, simultaneously securing your camera and protecting it against wind and rain. The waterproof housing features an integrated thermostat, 12 V DC (1.5 A) power supply unit and two 230 V AC heating elements. These heating elements prevent condensation and mist from forming on the window of the housing, ensuring clear pictures no matter the weather. The housing is dust-proof and protected against powerful water jets (IP68), so it can be used in any outdoor environment.

Technical Data:

IK protection class	10
Dimensions	(W x H x D) 154 x 123 x 410 mm
Width	154 mm
Housing material	aluminium
Heating	Yes
Height	123 mm
Cabling	internal
Length	410 mm
Power consumption	30 W

Max. operating temperature	50 °C
Min. operating temperature	-45 °C
Net weight	3,4 kg
Power supply unit	12 VDC / 1,5 A
Tamper protection	Cover switch
IP protection class	68
AC voltage supply	230 V
Certifications	CE, RoHS, REACH