

## HAR42EL



FULL BODY HARNESS - 2 ANCHORAGE POINTS - DIELECTRIC

Ref. HAR42EL\_



### Product specifications

Dielectric harness. 2 fall arrester anchorage points (back - front). 4 adjustable buckles. Buckles with plastic coating. Material insulates to 20kV.

Straps: Polyester.

Buckles: 100% plastic coating.

#### COLOUR

Black-Grey

#### SIZE

S/M/L, XL/XXL

## Product Use - Risks



Fall



Construction / Civil engineering



Heavy industry



Services / Logistics



Oil / Gas



Wind energy



Vertical movement on a permanent structure



Long vertical movement or movement on

inclined surface



Short vertical movement or movement on inclined surface (less than 3 m)



Vertical movement, confined space



Long movement with multi connection /disconnection



Long horizontal movement on horizontal surface



Long horizontal movement on vertical structure



Short horizontal movement (less than 3 m)

## Product's highlights & user's benefits

DIELECTRIC

## Certifications and Standards



PPE DIRECTIVE 89/686/EEC

EN363 : 2008 Personal fall protection equipment - Personal fall protection systems

EN364 : 1992 Personal fall protection equipment : Test method

EN365 : 2004 General requirements for the instructions for use and the marking

EN361 : 2002 Personal protection equipment against falls from a height - Full body harnesses

## References

References	Bar code	COLOUR	SIZE		
HAR42ELGT	3295249203481	Black-Grey	S/M/L	5	-
HAR42ELXX	3295249203498	Black-Grey	XL/XXL	5	-