



Zip® 750MB FireWire® drive technical specifications

Document #11441e.html

Performance: (**Note** : Specs marked as "with Zip 750MB disk" may be reduced when using Zip® 100MB or Zip 250MB disks)

- **Seek Time** (avg.): 29.0 ms
- **Maximum Sustained Transfer Rate**: 7.5 MB/sec (with Zip 750MB disks)
- **Rotational Speed**: 3676 RPM

Reliability:

- **Error Rate**: <1 error in 3e+12 bits

Operating Environment:

- **Temperature**:
 - **Operating**: 10° to 50.5° C
 - **Shipping**: -40° to 60° C
- **Relative Humidity**:
 - **Operating**: 20 to 80% non-condensing
- **Vibration**:
 - **Operating**: 0.7G (5-17 Hz); 0.25G (17-225 Hz)
 - **Non-Operating**: 1.2G (7-28 Hz); 2G (28-62 Hz); 5G (62-225 Hz)
- **Shock**:
 - **Operational**: 7.5G, ½ sine wave for 11 ms
 - **Non-Operational**: 10.0G for 11 ms
- **Drop Shock**: 200G (2 ms); 100G (11 ms)

Physical Description:

- **Size/Dimensions** (L x W x H): 175mm x 110mm x 21mm
- **Weight**: 180g
- **Interface**: IEEE-1394/FireWire®

General Features:

- **Disk Storage Capacity**: 750MB / 250MB (read/write-compatible) / 100MB (read-only)
- **Read/Write Protection**: Yes, via software
- **Hot Plug and Play**: Yes