

HIGH PRECISION DRILLING IN MULTIPLE MATERIALS

EXPERT HEX-9 Multi Construction Drill Bit

EXPERT

- ① Accurate drilling is easier with Bosch Centering Geometry
- ② Start holes accurately with a specially designed centring tip
- ③ High-performance carbide tip manufactured by fine grinding
- ④ Optimised dust extraction channel for fast, efficient drilling



CENTERING
GEOMETRY

UP TO
5x*

PRECISION

* vs. Bosch CYL-3



BOSCH

EXPERT HEX-9 MULTI CONSTRUCTION DRILL BIT



- Ideal for drilling holes into multiple materials. Can be used in impact mode on concrete and stone, and on rotary setting for brick, soft ceramic tile, sheet metal, wood and plastic
- Best for building trades: maximum precision and highly versatile
- Up to 5x more precise than a Bosch CYL-3 Drill Bit
- Hex shank for a strong connection and maximum torque transmission in three-jaw chucks and 1/4" internal hex tool holders



PRODUCT PROPERTIES						ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Diameter (D) Inch	Total length mm	Working length Inch	Total length Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number
3.00	45		90			PC1d	1	5	538 624	2 608 900 569
3.50	45		90			PC1d	1	5	245 373	2 608 902 346
4.00	45		90			PC1d	1	5	538 631	2 608 900 570
4.00	90		150			PC1d	1	5	245 380	2 608 902 347
5.00	50		100			PC1d	1	5	538 648	2 608 900 571
5.00	90		150			PC1d	1	5	245 397	2 608 902 348
5.50	60		100			PC1d	1	5	538 655	2 608 900 572
5.50	90		150			PC1d	1	5	538 662	2 608 900 573
6.00	60		100			PC1d	1	5	538 679	2 608 900 574
6.00	90		150			PC1d	1	5	538 686	2 608 900 575
6.00	200		250			PC1d	1	1	245 441	2 608 902 353
6.50	60		100			PC1d	1	5	538 709	2 608 900 577
6.50	90		150			PC1d	1	5	245 403	2 608 902 349
6.50	200		250			PC1d	1	1	245 458	2 608 902 354
7.00	60		100			PC1d	1	5	538 723	2 608 900 579
7.00	90		150			PC1d	1	5	538 730	2 608 900 580
7.00	200		250			PC1d	1	1	245 465	2 608 902 355
8.00	50		100			PC1d	1	5	538 747	2 608 900 581
8.00	90		150			PC1d	1	5	245 410	2 608 902 350
8.00	200		250			PC1d	1	1	245 472	2 608 902 356
8.00	350		400			PC1d	1	1	245 533	2 608 902 362
9.00	90		150			PC1d	1	5	245 427	2 608 902 351
10.00	90		150			PC1d	1	5	538 754	2 608 900 582
10.00	200		250			PC1d	1	1	245 489	2 608 902 357
10.00	350		400			PC1d	1	1	245 540	2 608 902 363
11.00	90		150			PC1d	1	5	245 434	2 608 902 352
12.00	90		150			PC1d	1	5	538 761	2 608 900 583
12.00	200		250			PC1d	1	1	245 496	2 608 902 358
12.00	350		400			PC1d	1	1	245 557	2 608 902 364
14.00	150		200			PC1d	1	1	245 502	2 608 902 359
14.00	200		250			PC1d	1	1	245 519	2 608 902 360
16.00	150		200			PC1d	1	1	245 526	2 608 902 361
16.00	350		400			PC1d	1	1	245 564	2 608 902 365
		1/8		2	3	PC1d	1	5	587 059	2 608 901 457
		5/32		4	6	PC1d	1	5	587 066	2 608 901 458
		3/16		4	6	PC1d	1	5	587 073	2 608 901 459
		1/4		4	6	PC1d	1	5	587 080	2 608 901 460



BOSCH

EXPERT HEX-9 MULTI CONSTRUCTION DRILL BIT

PRODUCT PROPERTIES						ORDERING INFORMATION					
Diameter (D) mm	Working length mm	Diameter (D) Inch	Total length mm	Working length Inch	Total length Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode 4 059 952...	Part number	
		1/4	6	6	8	PC1d	1	5	587 097	2 608 901 461	
		5/16	4	6	6	PC1d	1	5	587 103	2 608 901 462	
		5/16	8	10	10	PC1d	1	1	587 110	2 608 901 463	
		3/8	4	6	6	PC1d	1	5	587 127	2 608 901 464	
		3/8	8	10	10	PC1d	1	1	587 134	2 608 901 465	
		1/2	4	6	6	PC1d	1	5	587 141	2 608 901 466	
		1/2	8	10	10	PC1d	1	1	587 158	2 608 901 467	



BOSCH