

incandescent lamp, 115 V AC, 5 W, Base BA 15d, accessory for signaling columns, with diameters 50 mm + 70 mm, (Packing unit 10 units)



General technical data	
Product brand name	SIRIUS
Product designation	Incandescent lamp
Type of voltage of the operating voltage	AC
Operating voltage	
• 1 at AC at 50 Hz rated value	115 V
• 1 at AC at 60 Hz rated value	115 V
Relative positive tolerance of the operating voltage	10 %
Relative negative tolerance of the operating voltage	-10 %
Reference code	
• acc. to DIN EN 61346-2	P
• acc. to DIN EN 81346-2	P

Mechanical data	
Outer diameter of the signal column element	70 mm

Lamp	
Type of light source	filament lamp
Mounting type	BA 15d

Ambient conditions	
--------------------	--

Ambient temperature during operation	-20 ... +50 °C
Height	42 mm
Width	16 mm

Certificates/ approvals

General Product Approval	EMC	Shipping Approval			
 UL		 RCM	 ABS	 PRS	 RINA

other

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

www.siemens.com/sirius/catalogs

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4348-1XX>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4348-1XX>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD4348-1XX>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4348-1XX&lang=en

last modified:

09/24/2020