

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84729-0006](#)
Status: **Active**
Overview: Sealed Industrial USB Solutions
Description: Sealed Industrial USB Type B Plug-to-Shielded Pigtail, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-84727-002 \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	84729
IP Rating	IP67
Overview	<u>Sealed Industrial USB Solutions</u>
Product Name	RJ45
Type	Single Ended (pigtail)
UPC	822348832521

Physical

Coupling Type	Overmolded Cable
Gender	Female
Keyway	N/A
Length	N/A
Material - Component	Nylon
Mounting Thread Size	N/A
Orientation	N/A
Panel Mount	N/A
Poles	4
Temperature Range - Operating	-20°C to +60°C
Wire Size AWG	28
Wire/Cable Type	USB

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers

Product Specification	PS-84727-002
Sales Drawing	SD-84729-006



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[84729Series](#)

Mates With

[84727 Sealed Industrial USB 2.0 Type A
 Plug to Shielded Pigtail Receptacles](#)