

Technical data sheet

Article number:
151-04629

HSRC72

Product Group	Releasable cable clip for screw fixation/with pipe/tube holder, M6, Dmax=37mm
Product Family	Art.-No. 151-04629 HSRC72-PA666V0-BK
Material	Polyamide 6.6/6, V0 (PA666V0)
Colour	Black (BK)
Bundle Ø max.	37 mm
Bundle Ø min.	27 mm
CE Certification	No
Fixation Method	Bolt
Flammability	UL 94 V0
for Hole Ø (FH)	M6
Height (H)	72 mm
Length (L)	175 mm
Mounting Screw Type	M6 Screw
Operating Temperature	-40 °C to +120 °C
Package Content	40
Package Content packed in	box
ROHS compliant	Yes
Specifications	EN 45545-2
UV-Stabilised	Yes [Raw Material based]
Width (W)	79 mm



EN 45545-2