

# Product data sheet

Specifications



## Spacial SF/SM single chassis coupling set - 432 modules of 18 mm - 2000x800 mm

NSYCSH208

### Main

|                                    |  |
|------------------------------------|--|
| Range                              | Spacial  |
| Accessory / separate part category | Mounting accessory   |
| Application                        | Multi-purpose  |
| Product or component type          | Coupling kit   |
| For enclosure nominal dimensions   | -  |
| Mounting location                  | Front of enclosure   |
| Range compatibility                | Spacial SM<br>Spacial SF   |
| Device composition                 | fixing elements<br>2 horizontal crossbars<br>2 vertical uprights |
| Quantity per set                   | Set of 1   |

### Complementary

|                               |                                   |
|-------------------------------|-----------------------------------|
| Material                      | Steel                             |
| Colour                        | Grey (RAL 7035)                   |
| Surface finish                | Epoxy-polyester powder            |
| Fixing mode                   | By fixing element                 |
| Total number of 18 mm modules | 432                               |
| Height                        | 1905 mm real:<br>2000 mm nominal: |
| Width                         | 702 mm real:                      |
| Depth                         | 100 mm real:                      |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Weight             | 7.86 kg |
| Package 1 Height             | 5.5 cm  |
| Package 1 width              | 12 cm   |
| Package 1 Length             | 200 cm  |

## Offer Sustainability

---

|                                   |   |
|-----------------------------------|---|
| <b>Sustainable offer status</b>   | Green Premium product   |
| <b>REACH Regulation</b>           | <a href="#">REACH Declaration</a>   |
| <b>REACH free of SVHC</b>         | Yes   |
| <b>EU RoHS Directive</b>          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>                     |
| <b>Mercury free</b>               | Yes   |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>   |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| <b>Environmental Disclosure</b>   | <a href="#">Product Environmental Profile</a>   |

---

## Contractual warranty

---

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

---