

Features

- UL approved Nylon 66
- UL94V-2 flame rated
- Low Smoke, Halogen Free
- Max operating temperature 85°C

RS PRO Cable Ties

RS Stock No.: 0828975



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Designed for demanding cable management tasks, this cable tie offers exceptional strength and reliability. Made from fire-resistant Nylon 66 (UL-approved) with a flame-rating of 94V-2, it's built to deliver robust performance even in harsh environments. Whether in construction, telecom, data centres, or high-power installations, this cable tie helps keep things neat, safe, and resilient.

General Specifications

Series	Nylon Cable Ties
Type	Non-Releasable
Colour	Natural
Material	Nylon 66
Finish	Smooth
Application	Designed for quick installation and bundling of cables
Resistant To	Not specified
UV Resistant	No
Minimum Operating Temperature	Not specified
Maximum Operating Temperature	85°C
Fire Behaviour	Self-Extinguishing
Quantity	100

Mechanical Specifications

Length	75mm
Width	2.5mm
Tensile Strength	80N

Approvals

Declarations	RoHS
---------------------	------

Standards Met	UL
---------------	----

