



BRUSHLESS

DEWALT 18V XR Brushless Body Grip Jigsaw – Bare Unit

DCS335N-XJ



- Brushless motor provides improved runtime and durability
- Slide switch with No Volt release for ergonomics and safety
- 4-position pendulum action controls the aggressiveness or smoothness of cuts
- Tool free adjustable shoe with anti scratch cover bevels to 45 degrees in both directions
- Quick and easy keyless blade change system accepts T- shank blades
- Overmoulded soft grip on body provides additional user comfort and reduces user fatigue
- Dust blower ensures first-rate cut and view
- Dual LED lights illuminate cut line for enhanced visibility

Description:

The DEWALT 18V XR Jigsaw with Body Grip Handle – Bare Unit has a Brushless motor which offers increased runtime and performance, delivering up to 3200 strokes per minute, making cutting applications faster. The tool free blade change mechanism holds the blade more securely and keeps the blade squarer during use for the ultimate precision. Dual LED's and a built in dust blower keep the workpiece free from debris for the most accurate cut or switch to the included dual sided Airlock compatible extraction kit. The Slide switch with No-volt release prevents the unit from starting unintentionally when locked on for added safety. (Battery Not Included)

Supplied With:

- 1 x Anti Scratch Shoe Cover
- 1 x Dust Port Airlock Compatible
- 1 x Anti Splinter Insert

Specifications	
Power	18V
Max Cutting Capacity (Wood)	135MM
Max Cutting Capacity (Aluminum)	25MM
Max. Cutting Capacity (Steel)	10MM
Weight	2KG
Hand/Arm Vibration - Cutting boards	13.3 m/s ²
Hand/Arm Vibration - Cutting sheet metal	8.1 m/s ²