

Main

Range of product	Odace
Range	Odace
Product or component type	Audio/video socket
Device presentation	Mechanism with fixing frame
Connector type	HDMI
Electrical circuit type	Video Audio
Colour tint	Aluminium
Type of packing	Group

Complementary

Device mounting	Flush
Socket number	1
Fixing mode	By screws
Surface finish	Matt
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: fixing frame
Height	71 mm
Width	71 mm
Depth	41.7 mm
Embedding depth	25.7 mm
Net weight	0.059 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	-5...40 °C
Standards	EN 50157 EN 50049
IP degree of protection	IP21
IK degree of protection	IK04

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes