

Rechargeable LED floodlight EL 4000 MA 4000 lm, IP54

For indoor and outdoor use, IP 54.



Product number 1173700017
EAN 4007123700028

DESCRIPTION

- Solid, modern aluminium housing.
- Space-saving thanks to foldable frame.
- Switch with 100 % / 50 % dimming function.
- Sturdy tubular steel frame with plastic protective corners and ergonomically shaped plastic carrying handle.
- Spotlight can be continuously swivelled and locked.
- Suitable for mounting on brennenstuhl® tripods.
- With integrated Li-Ion battery 3.7 V / 11 Ah and battery status indicator on the back.
- Includes power bank function and 1x USB charging cable.

TECHNICAL DATA

Luminous flux	4000 lm
Power consumption	50 W
Colour temperature	6500 K
Nominal input voltage	5 V
Cable length	1 m
Battery capacity	11 Ah
Battery voltage	3.7 V
Light duration max.	6 h

Battery charging time approx.	6 h
Battery type	Battery pack
Battery technology	Lithium-ion
Impact strength	IK08
Protection class	III
Degree of protection (IP)	IP54
Colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1
Weight of product (without packaging)	1.59 kg
Dimension LxWxH (without packing)	7.9 cm x 28.2 cm x 30.5 cm

Weight of product (including packaging)	1.83 kg
Dimension LxWxH (incl. packing)	9 cm x 29.5 cm x 31.5 cm

SCOPE OF DELIVERY

Rechargeable LED floodlight EL 4000 MA