



**K37ID**

FICHE TECHNIQUE

# CHERRY K37ID

COMPACT INDUSTRIAL PERFORMANCE FOR MODERN WORKSPACES.

The CHERRY K37ID is a compact industrial keyboard designed for reliable operation in demanding work environments. Featuring IP54 protection against dust and splashing water, it delivers dependable performance for production, logistics, workshop, and automation applications. Its space-saving 98-key layout, industrial durability, and competitive pricing make it an ideal solution for scalable industrial deployments.



## POINTS FORTS

- IP54 Protection: Reliable resistance against dust and splashing water for everyday industrial use.
- Compact 98-Key Design: Saves valuable workspace without sacrificing essential functionality.
- Mem-chanical Typing Feel: Membrane keyboard technology with a precise, tactile typing experience inspired by mechanical keyboards.
- Reduced Downtime: Durable construction helps minimize maintenance interruptions and replacement cycles.
- Ideal for Scalable Rollouts: Cost-efficient deployment across multiple industrial workstations.
- Better Value-to-Protection Ratio: Industrial protection and reliability without premium pricing.

## CONTENU DE LA LIVRAISON

- Clavier
- Manuel

# CARACTÉRISTIQUES TECHNIQUES

## INFORMATIONS SUR LE PRODUIT

|                               |                                                                                                                     |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Référence                     | JK-3700DE-2                                                                                                         |
| EAN                           | 4025112123733                                                                                                       |
| Disposition                   | DE (Allemagne)                                                                                                      |
| Numéro de modèle              | JK-37                                                                                                               |
| Garantie                      | Garantie limitée supplémentaire d'un an offerte par le fabricant                                                    |
| Homologations du produit      | <ul style="list-style-type: none"><li>- CE</li><li>- UKCA</li><li>- FCC</li><li>- REACH</li><li>- RoHS UE</li></ul> |
| Assistance logicielle         | CHERRY KEYS                                                                                                         |
| Système d'exploitation        | Windows                                                                                                             |
| System Requirements-Hardware  | USB-A                                                                                                               |
| Dimensions, emballage compris | 390 mm × 165 mm × 43 mm   955 g                                                                                     |

## TEMPÉRATURE

|                                        |       |
|----------------------------------------|-------|
| Température minimale de fonctionnement | 0 °C  |
| Température de fonctionnement max.     | 40 °C |

## CLAVIER

|                      |     |
|----------------------|-----|
| Matériau des touches | ABS |
| Éclairage            | Non |
| Pieds réglables      | oui |

---

Consommation électrique maximale (mA) du clavier 20 mA

---

|                   |                         |
|-------------------|-------------------------|
| Format du clavier | Taille standard (100 %) |
|-------------------|-------------------------|

---

|                |     |
|----------------|-----|
| N-Key Rollover | oui |
|----------------|-----|

---

|               |     |
|---------------|-----|
| Anti-ghosting | oui |
|---------------|-----|

---

|                      |     |
|----------------------|-----|
| Remplacement à chaud | non |
|----------------------|-----|

---

© Cherry Europe GmbH

Cherrystraße 2 · 91275 Auerbach/OPf. · Germany

**cherry-world.com · cherry.de**

Sales Support · Technischer Support · eHealth Support

**+49 9643 - 2061 - 100**

**[www.cherry.de/de-de/kontakt](http://www.cherry.de/de-de/kontakt)**

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products.