

SIMATIC S7-300, INTERFACE MODULE IM 361 IN EXPANSION RACK FOR CONNECTING TO CENTRAL RACK (IM360), 24 V DC SUPPLY VOLTAGE, WITH K-BUS



Figure similar

Supply voltage	
Rated value (DC)	
• 24 V DC	Yes
Input current	
from supply voltage L+, max.	500 mA
Power loss	
Power loss, typ.	5 W
Hardware configuration	
Number of interfaces per CPU, max.	3
Dimensions	
Width	80 mm
Height	125 mm
Depth	120 mm
Weights	
Weight, approx.	505 g
last modified:	13.02.2016