

blue mushroom Ø40 mm pushbutton head Ø22 latching turn to release

Local distributor code:

398140575 ZB4BS56

EAN Code: 3389110523324

Main

Range of product	Harmony XB4	
Product or component type	Head for non-illuminated push-button	
Device short name	ZB4	
Bezel material	Black metal	
Mounting diameter	22 mm	
Sale per indivisible quantity	1	
Head type	Standard	
Shape of signaling unit head	Round	
Type of operator	latching	
Reset	Turn to release	
Operator profile	Blue mushroom Ø 40 mm, unmarked	

Complementary

CAD overall width	40 mm	
CAD overall height	40 mm	
CAD overall depth	57 mm	
Net weight	0.07 kg	
Mechanical durability	300000 cycles	
Electrical composition code	C11 for <3 contacts using single blocks in front mounting C15 for <1 contacts using single blocks in front mounting C7 for <4 contacts using single blocks in front mounting C8 for <4 contacts using single and double blocks in front mounting C10 for <4 contacts using single and double blocks in front mounting	

Environment

Protective treatment	тн	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-4070 °C	
Overvoltage category	Class I conforming to IEC 60536	
IP degree of protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K	
NEMA degree of protection	NEMA 13 NEMA 4X	

IK degree of protection	IK06 conforming to IEC 50102	
Standards	EN/IEC 60947-5-4 UL 508 EN/IEC 60947-5-1 JIS C8201-5-1 CSA C22.2 No 14 EN/IEC 60947-5-5 EN/IEC 60947-1 JIS C8201-1	
Product certifications	BV CSA DNV LROS (Lloyds register of shipping) UL listed	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.800 cm
Package 1 Width	4.400 cm
Package 1 Length	5.400 cm
Package 1 Weight	71.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	25
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	1.975 kg
Unit Type of Package 3	P06
Number of Units in Package 3	800
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	71.200 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No