



RS Code - 454-1274
Part No. 1678UHO050P40

Steel sheet housing, broad reinforced fork, two ball races, fixed castor, polyamide wheel, Rubber tread, plain bearing with threadguards, 50 mm wheel diameter, square plate.

Technical Data

| Attribute | Value |
|-------------------------|------------|
| Wheel Diameter | 50mm |
| Load Capacity | 55kg |
| Mounting Type | Plate |
| Overall Height | 72mm |
| Rotation | FIXED |
| Wheel Width | 22mm |
| Fixing Plate Dimensions | 60 x 60mm |
| Tyre Material | Rubber |
| Includes Brake | No |
| Fixing Centres | 48 x 48mm |
| Weight Class | Light Duty |
| Number of Fixing Holes | 4 |
| Hub Bearing Type | Plain Bore |
| Fixing Hole Size | 6mm |
| Hub Material | PP |