



PRODUCT-DETAILS

DPMP-02

DPMP-02; Control panel mounting platform (surface) DPMP-02



General Information

Global Commercial Alias	DPMP-02
Product ID	3AXD5000009374
ABB Type Designation	DPMP-02
EAN	6438177339014
Catalog Description	DPMP-02; Control panel mounting platform (surface) DPMP-02
Long Description	DPMP-02 control panel mounting platform is for surface mounting. The mounting platform does not include the control panel.

Ordering

Customs Tariff Number	85049090
HS Code	850490 -- ELECTRICAL MACHINERY AND EQUIPMENT AND PARTS THEREOF; SOUND RECORDERS AND REPRODUCERS, TELEVISION IMAGE AND SOUND RECORDERS AND REPRODUCERS, AND PARTS AND ACCESSORIES OF SUCH ARTICLES;Electrical transformers, static converters (for example, rectifiers) and inductors;Parts
Invoice Description	Control panel mounting platform (surface) DPMP-02
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0.17 kg 0.375 lb
Product Net Depth / Length	0 mm 0.000 in
Product Net Height	0 mm 0.000 in
Product Net Width	0 mm 0.000 in
Package Level 1 Depth / Length	156 mm
Package Level 1 Height	82 mm
Package Level 1 Width	224 mm
Package Level 1 Units	1 carton

Certificates and Declarations

Declaration of Conformity - CE	3AXD10001818627
REACH Date	20250523
REACH Information	No data - If REACH inform is not yet available for a certain product
RoHS Date	20240508
RoHS Declaration	3AXD10001818627
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Technical

Frame Size	Undefined
------------	-----------

External Classifications and Standards

ETIM 9	EC002025 - Accessories/spare parts for frequency controller
UNSPSC	39122004

Environmental

WEEE Category	Product Not in WEEE Scope
---------------	---------------------------

Categories

Drives → Drive Options → User Interface Options → DPMP-02 - Panel surface mounting kit

Drives → Services → Spares and Consumables → Parts

Drives → Services → Spares and Consumables → Parts

