



Features

• Highlight your garden with our adjustable spike light, featuring a tiltable head for precise illumination. Available in warm white (3000K) and cool white (4000K), this IP65-rated light is perfect for flower beds, trees, and outdoor landscapes. With a durable design, a long 30,000-hour lifetime, and a 3-year warranty, it's built to shine in any weather

Product Overview

Product name	YOURHOME SYLSPIKE 600LM 4000K
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Other
General application	Residential & Consumer
ETIM Class	EC000758
Fixture luminous flux (lm)	600
Luminaire efficacy (lm/W)	90
Correlated colour temperature (k)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	30
Photobiological Risk Group	RG1
Total power consumption (W)	6.7

## YOURHOME SYLSPIKE 600LM 4000K 0090195

Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Housing colour	RAL9005
IP rating	IP65
IK rating	IK05
Product EAN number	5410288901954
Warranty	3 years
Dimming method	N/A

### Data table

#### GENERAL DATA

Product name	YOURHOME SYLSPIKE 600LM 4000K
Technology	LED
Cap/Base	N/A
Housing	Aluminium
Mount	Other
General application	Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC000758
Warranty	3 years

#### OPTICAL DATA

Fixture luminous flux (lm)	600
Luminaire efficacy (lm/W)	90
Correlated colour temperature (k)	4000
Light colour	Cool White
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	30
Distribution type	Symmetric

## YOURHOME SYLSPIKE 600LM 4000K 0090195

Photobiological Risk Group	RG1
----------------------------	-----

### ELECTRICAL DATA

Total power consumption (W)	6.7
Primary Supply/Product voltage - min (V)	220.0
Primary Supply/Product voltage - max (V)	240.0
Lamp power factor	0.55
THD (at 230 V, 50 Hz, full load, at 100% dimming level) $\leq$ xx.x %	200
Electrical protection	Class I
Control gear required	No
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Inrush Current (A)	9.12
Inrush Duration ( $\mu$ s)	100
Energy Efficiency Class (A->G) of contained light source	F
Nominal Frequency (Hz)	50/60Hz

### LIFETIME DATA

Lifespan L70 B50	42000
------------------	-------

### PHYSICAL DATA

Housing colour	RAL9005
IP rating	IP65
IK rating	IK05
Diffuser finish	Other
Diffuser material	None
Nominal Product Length (mm)	131
Nominal Product Width (mm)	60
Nominal Product Height (mm)	218
Weight (kg)	0.35



YOURHOME SYLSPIKE 600LM 4000K  
0090195

PACKAGING

Product EAN number	5410288901954
Packaging single length / height (cm)	21.0
Packaging single width (cm)	10.5
Packaging single depth (cm)	6.5
DUN14 (inner)	15410288901951
Units per outer package	10
Packaging outer length / height (cm)	23.0
Packaging outer width (cm)	34.5
Packaging outer depth (cm)	23.0

SAFETY DATA

Glow Wire Test (°C)	650
Optimal operating condition (°C)	-20-40
Special purpose lamp	No
Dry applications use only	No
Suitable for household illumination	No