



CPWplus Weighing Scales

The CPWplus series of scales offers an extensive range of models and configurations to accommodate a variety of applications. Choose the basic CPWplus for compact portability, the -M or -L for large platforms. Simple operation, a selection of platform sizes, battery and AC operation, and rugged construction all combine to make the CPWplus truly a great value in this industrial range.



CPWplus Weighing Scales

Features

- Vivid, backlit LCD easily visible in any lighting conditions
- Programmable backlight can be set to "always on", "always off" or "light only when weighing"
- Colour-coded keys facilitate quick recognition of the most frequently used buttons
- Large, grade 304 stainless steel pan allows easy cleaning
- Lightweight design simplifies transport and portability
- Rugged construction stands up to industrial use
- Splash-proof housing, keypad and display mean easy cleaning and peace of mind
- Wall-mount bracket for placing indicator on vertical surface

- Auto power-off to save energy
- External calibration allows for verification and adjustment with weights
- Hold function freezes the displayed weight, allowing time to lapse without losing the result
- Selectable digital filtering helps minimise effects of vibration and disturbances
- Zero-tracking feature ensures display returns to zero reading

Applications

- Weighing
- Display hold

Model	CPWplus 6	CPWplus 15	CPWplus 35 CPWplus 35M CPWplus 35L	CPWplus 75 CPWplus 75M CPWplus 75L	CPWplus 150 CPWplus 150M CPWplus 150L	CPWplus 200 CPWplus 200M CPWplus 200L	CPWplus 300L
Capacity	6kg	15kg	35kg	75kg	150kg	200kg	300kg
Readability	0.002kg	0.005kg	0.01kg	0.02kg	0.05kg	0.05kg	0.1kg
Repeatability (S.D.)	2g	5g	10g	20g	50g	50g	100g
Linearity (+/-)	4g	10g	20g	40g	100g	100g	200g
Tare Range	Full range						
Pan Size			300x300mm	500x500mm (M)	900x600mm (L)		
Weighing Units	kg, lb, lb:oz, oz						
Stabilisation Time (sec)	2						
Interface	RS-232						
Calibration	External calibration						
Display	Backlit LCD with 22mm-high digits						
Power Supply	12VAC 150mA adapter / 6 x AA batteries 12VDC 500mA adapter / Internal rechargeable battery (M & L)						
Operating Temperature	0° to 40°C						
Housing	Extruded aluminum						
Overall Dim.			300x300x50mm	500x500x40mm (M)	900x600x80mm (L)		
Net Weight			4.00kg	8.90kg (M)	14.40kg (L)		

With more than forty years of experience in the production of balances and scales, professionals worldwide rely on Adam for feature-rich, quality products with best-in-class value - The right balance of speed, performance and value.

Supplied by:

Accessories

- 700100099 Hard carrying case w/lock
- 1120011156 ATP Adam thermal printer
- 3126011263 ATP printer paper
- 3126011281 ATP printer paper (pack of 10)
- 700200059 Non-slip rubber mat (CPWplus L only)
- 3074010266 RS-232 cable (null-modem)
- 3074010507 RS-232 to USB adapter (must order corresponding RS-232 cable)
- 600002028 Adam DU data collection program